



# Medical

## Transport systems

Universal products for the safe transport of medical goods.

.....

Product overview	112–113
W 105 N cupboard trolley	114–121
Interior fittings for cupboard trolleys	122
Accessories for cupboard trolleys	123
W 170/W 171/W 172 box trolleys	124–128
Accessories for box trolleys	129
W 161 spring-loaded trolleys	130
W 181/W 182 transport trolleys	131
Shelf trolleys & Variomobil	132
Driverless transport systems	133
Cage trolleys	134
Data disposal	135



W 105 N cupboard trolley for laundry transport



W 171 transport trolley for waste transport



W 161 spring-loaded trolley for ergonomic working



W 105 N cupboard trolley for laundry supplies



W 105 N cupboard trolley for transportation and storage of materials



W 105 N cupboard trolley for operational areas



Internal supply with the W 105 N cupboard trolley

# Top quality is always a question of details.

The cupboard trolley for the safe, hygienic and practical storage and transportation of laundry, medicines, consumable and other durable goods. The user groups include

hospitals, clinics, laundries, industry, the catering trade and public authorities.



# Perfectly equipped for a hard day's work.



## W 105 N cupboard trolley

**1 Trolley top.** Equipped with a front bumper as standard, bumper can be added at the back if required, and suitable for transport by lorry. **2 Peripheral door seal.** Between the body and the door leaves, suitable for cleaning in washdown facilities and provides protection against dust. **3 Ergonomic handle.** Made from ergonomically shaped aluminium section. **4 Door lock.** Ergonomically shaped and can be fitted with a lead seal, easy-to-operate lever with locking function at the top and bottom ensures reliable closing, suitable for transport by lorry. **5 Bumper.** Abrasion- and disinfectant-resistant plastic padding, easy to replace. **6 Chassis.** 2 swivel and 2 fixed castors, corner-mounted, easy running, rubber wheels, "non-marking," roller bearings, thread guards, wheel brakes optional. **7 Doors.** Doors open 270°, doors secured by magnetic catch.

Practical cupboard trolley for fresh laundry, dirty laundry and much more.



### Universal cupboard trolley W 105 N

- ▶ Aluminium cupboard trolley, anodised, for a wide variety of applications.
- ▶ Smooth interior, no inaccessible areas – easy to clean.
- ▶ Supplied as standard with fixed additional shelf (excluding 41861 and 46862).
- ▶ Optionally with individual interior fittings.
- ▶ Ergonomically shaped, anodised aluminium handle, on swivel castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø 200 mm, easy running, rubber wheels, “non-marking,” with thread guards.
- ▶ Also suitable for container washdown facilities if appropriate special running-gear castors are used.



Int. length, approx. mm	1,120	1,120	1,250	790	790	1,120	1,250
Int. width, approx. mm	550	550	620	550	550	550	620
Int. height, approx. mm	1,415	1,030	1,415	1,415	1,030	1,415	1,415
Ext. length, approx. mm	1,260	1,260	1,390	930	930	1,260	1,390
Ext. width, approx. mm	630	630	700	630	630	630	700
Ext. height, approx. mm	1,735	1,355	1,740	1,740	1,355	1,735	1,740
Volume, approx. l	870	630	1,090	610	445	870	1,090
Weight, approx. kg	72.0	65.0	84.0	66.0	56.0	64.0	76.0
Order No.	41850	41851	41852	41854	41858	41861	41862

Sterile, fresh or used:  
the ergonomically designed transport trolleys for laundry.



### W 105 N cupboard trolley for laundry

- ▶ Aluminium cupboard trolley, anodised, for transporting laundry.
- ▶ Smooth interior, no inaccessible areas – easy to clean.
- ▶ 2 additional shelves, bottom shelf can be folded down towards the front, the top shelf towards the rear.
- ▶ Ergonomically shaped, anodised aluminium handle, on swivel castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø 200 mm, easy running, rubber wheels, “non-marking,” with thread guards.
- ▶ Also suitable for container washdown facilities if suitable special running-gear castors are used.



### W 105 N operating theatre cupboard trolley

- ▶ Aluminium cupboard trolley, anodised, for transporting sterile fresh-laundry packs and dirty laundry.
- ▶ Smooth interior, no inaccessible areas – easy to clean.
- ▶ Two additional shelves, both can be folded down towards the front.
- ▶ Ergonomically shaped, anodised aluminium handle, on swivel castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø125 mm, easy running, rubber wheels, “non-marking,” with thread guards.
- ▶ Also suitable for container washdown facilities if suitable special running-gear castors are used.

Order No.	Inside dimensions, L × W × H, approx. mm	Outside dimensions, L × W × H, approx. mm	Weight, approx. kg	Volume, l
379452	1,120 × 550 × 1,415	1,260 × 630 × 1,735	72.0	870

Order No.	Inside dimensions, L × W × H, approx. mm	Outside dimensions, L × W × H, approx. mm	Weight, approx. kg	Volume, l
41864	835 × 470 × 1,415	975 × 550 × 1,655	63.0	555



## Cupboard trolley for ZARGES modules.



### W 105 N modular cupboard trolley

- ▶ Aluminium cupboard trolley, anodised, for a wide variety of applications.
- ▶ Shelf insert for ZARGES ISO-standard modules.
- ▶ Fixed insert rails, ABS support rails ensure that the modules slide easily.
- ▶ Ergonomically shaped handle of anodised aluminium section on the swivel-castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø160 mm, easy running, rubber wheels, "non-marking," with thread guards.
- ▶ Swivel castors with wheel brakes.
- ▶ Also suitable for container washdown facilities if appropriate special running-gear castors are used.



Int. length, approx. mm	477	920	1,363	920
Int. width, approx. mm	620	620	620	620
Int. height, approx. mm	1,253	1,253	1,253	1,253
Ext. length, approx. mm	615	1,060	1,505	1,060
Ext. width, approx. mm	700	700	700	700
Ext. height, approx. mm	1,540	1,530	1,530	1,530
Volume, approx. l	370	710	1,055	710
Weight, approx. kg	45.0	67.0	78.0	62.0
Number of insert levels	1 × 8	2 × 16	3 × 8	2 × 8
Order No.	41869	41870	41871	41872

Equipped for every task: our flexible modular cupboard trolleys.



### W 105 N modular cupboard trolley with rolling tambour door

- ▶ Space-saving opening through rolling tambour door.
- ▶ Lockable with digital lock.
- ▶ Slide-in width 600 mm.
- ▶ Configure with ZARGES modules.
- ▶ Ergonomically shaped, anodised aluminium handle, on swivel castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø160 mm, easy running, "non-marking," with thread guards.
- ▶ Swivel castors with wheel brakes.



Int. length, approx. mm	699	1,368
Int. width, approx. mm	520	520
Int. height, approx. mm	1,379	1,379
Ext. length, approx. mm	837	1,506
Ext. width, approx. mm	600	600
Ext. height, approx. mm	1,655	1,655
Weight, approx. kg	58.0	84.0
Number of insert levels	1 × 23	2 × 23
Order No.	378948	373791



### W 105 N modular cupboard trolley with support wall

- ▶ Configure with ZARGES modules.
- ▶ Ergonomically shaped, anodised aluminium handle, on swivel castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø160 mm, easy running, rubber wheels, "non-marking," with thread guards.
- ▶ Swivel castors with wheel brakes.



Int. length, approx. mm	477	920
Int. width, approx. mm	620	620
Int. height, approx. mm	1,253	1,253
Ext. length, approx. mm	616	1,060
Ext. width, approx. mm	700	700
Ext. height, approx. mm	1,540	1,530
Weight, approx. kg	58.0	83.0
Number of insert levels	1 × 24	2 × 24
Order No.	379454	379453

Simple, safe and hygienic transport and storage.



### W 105 N modular cupboard trolley with shelf inserts

- ▶ Interior fittings: Installation frame for ZARGES ISO-standard modules.
- ▶ Insert rails can be hooked on in various positions.
- ▶ Slide-in width 600 mm.
- ▶ Ergonomically shaped, anodised aluminium handle, on swivel castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø160 mm, easy running, "non-marking," with thread guards.
- ▶ Swivel castors with wheel brakes.



Int. length, approx. mm	677	1,363
Int. width, approx. mm	550	550
Int. height, approx. mm	1,415	1,415
Ext. length, approx. mm	816	1,501
Ext. width, approx. mm	630	630
Ext. height, approx. mm	1,690	1,690
Weight, approx. kg	58.0	82.5
Number of insert levels	1 × 20	2 × 20
Order No.	379449	379450

### W 105 N storage cupboard trolley

- ▶ Aluminium cupboard trolley, anodised, for a wide variety of applications.
- ▶ 1/3 with installation frame for ZARGES ISO-standard modules, slide-in width 400 mm.
- ▶ 2/3 with 2 fixed shelf compartments.
- ▶ Ergonomically shaped handle of anodised aluminium section on the swivel-castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted, Ø160 mm, easy running, rubber wheels, "non-marking," with thread guards.
- ▶ Also suitable for container washdown facilities if suitable special running-gear castors are used.



Int. length, approx. mm	1,363
Int. width, approx. mm	620
Int. height, approx. mm	1,253
Ext. length, approx. mm	1,501
Ext. width, approx. mm	700
Ext. height, approx. mm	1,571
Weight, approx. kg	91.5
Number of insert levels	1.060
Order No.	379451

## Service made easy: cupboard trolleys for delivering meals.



### W 105 N food trolley Type 1

- ▶ Anodised aluminium cupboard trolley for hygienic food storage.
- ▶ With 6 compartments for Euronorm insulating trays.
- ▶ Ergonomically shaped handle of anodised aluminium section on the swivel-castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted,  $\varnothing$  200 mm, easy running, rubber wheels, "non-marking," with thread guards.
- ▶ Swivel castors with wheel brakes.
- ▶ Also suitable for container washdown facilities if suitable special running-gear castors are used.



### W 105 N food trolley Type 2

- ▶ Anodised aluminium cupboard trolley for hygienic food storage.
- ▶ With individual slide-in units for 33 Euronorm trays.
- ▶ Ergonomically shaped handle of anodised aluminium section on the swivel-castor side.
- ▶ Chassis: 2 swivel and 2 fixed castors, corner-mounted,  $\varnothing$  200 mm, easy running, rubber wheels, "non-marking," with thread guards.
- ▶ Swivel castors with wheel brakes.
- ▶ Also suitable for container washdown facilities if suitable special running-gear castors are used.

Order No.	Inside dimensions, L × W × H, approx. mm	Outside dimensions, L × W × H, approx. mm	Weight, approx. kg	Volume, l
41874	1,160 × 550 × 1,395	1,300 × 630 × 1,715	75.0	890

Order No.	Inside dimensions, L × W × H, approx. mm	Outside dimensions, L × W × H, approx. mm	Weight, approx. kg	Volume, l
41875	1,250 × 550 × 1,325	1,390 × 630 × 1,645	80.0	910

## The right solution, whatever your requirements: individual interior fittings.



### Fixed shelf compartments

For universal applications.



### Insert levels for ZARGES ISO-standard modules

ABS support rails ensure that the modules slide easily.



### Folding additional shelves

Safe and ergonomic working, suitable for transporting fresh or dirty laundry as well as waste in bags.



### Practical support systems for the ZARGES modular equipment range

Support wall, shelf compartment, insert rails, variable- and fixed-installation telescopic rails.



### Height of additional shelves adjustable by means of notched rails

Suitable for various packaging sizes.



### Removable additional shelves

Shelves can be used variably and cleaned separately.

## Accessories and customisation.



### Coloured markings

For customisation.



### Trolley-top bumper and reinforced corners

Protection of the trolley body during transport by lorry.



### Lock attachment

With identical and individual locking for safe transport.



### Drawbar and coupling for linking and moving trolleys in trains

For in-company transport (of up to a maximum of 5 trolleys).



### Label frames in various sizes

Simple holder for removable labels.



### Special castors

Stainless steel castors with directional lock, central stop and Total Stop, for a wide range of applications.



### Blackboard

For simple labelling on the trolley itself, self-adhesive and rewritable.



### Lead seal

To seal the container against unauthorised opening.



### Top railing

For securing items on the top of the trolley.